

MX SERIES

COOL LOOK, COOL COMFORT



6130 MX-6

The MX-5 and MX-6 are a cool and comfortable upgrade in earmuffs. The larger cup openings are designed to fit most ear sizes. The cushion-ribbed headband allows cool comfort all day long and the non-slip wire makes adjustments easy. The MX-5 and MX-6 are easy to wear and durable, have a sharp, cool look and increase compliance.

MX-5 AND MX-6

- Soft cushion-ribbed open air headband for cool comfort all day long
- Overmoulded headband is durable for rugged wear over many shifts
- Larger ear cushions allow freedom to fit almost all ears comfortably
- Lightweight wire frame allows easy cup adjustment yet holds its position for lasting comfort
- Cool looks and comfort to promote worker acceptance and compliance
- Extra soft foam/low pressure cushions and headband are PVC-Free
- Glossy surface for easy cleaning and longer wear
- Independently tested for protection you can count on
- MX-6 features exclusive waffled cup foam for superior protection
- PVC-Free for a greener alternative



6120 MX-5



6135 MX-6
Hygiene Kit



6125 MX-5
Hygiene Kit


MX SERIES

COOL LOOK, COOL COMFORT

INSTRUCTIONS FOR USE:

MX-5/MX-6 Series Earmuffs must be fitted and worn correctly to provide effective protection. Earmuffs and their cushions may deteriorate with use and should be examined for cracking or other deformations and replaced as necessary. Routinely wash with mild soap and water. The foam liner should be allowed to air dry before reinserting into the earmuffs.

- 1) With headband over-the-head, pull the cups outward and position over your ears so that they fully enclose the ear and seal tightly against the head.
- 2) Adjust the height of the cups until you have a tight and comfortable fit. For best results, remove all hair from under the cushions.
- 3) Maintenance: Replace cushions and foam inserts at least twice a year for hygiene and safety. For MX-5 order Part No. 6125 and for MX-6 order Part No. 6135.
For MX-6 only: Place the glossy side of the foam against the cup.



Ordering Information

| Part # | Description | SLC ₈₀ | Quantity Per Box/Bag | Quantity Per Case |
|--------|------------------|-------------------|----------------------|-------------------|
| 6120 | MX-5 Earmuff | 32dB/Class 5 | 1 Earmuff | 10 Boxes |
| 6130 | MX-6 Earmuff | 34dB/Class 5 | 1 Earmuff | 10 Boxes |
| 6125 | MX-5 Hygiene Kit | | 1 Kit | 20 Bags |
| 6135 | MX-6 Hygiene Kit | | 1 Kit | 20 Bags |

WARNING TO USER

1. Use this laboratory-derived attenuation data for comparison purposes only. The amount of protection afforded in field use often is significantly lower depending on how the protectors are fitted and worn.
2. Failure to follow all instructions could result in hearing loss or injury.
3. Failure to obtain a proper fit will reduce effectiveness of hearing protectors and could result in hearing loss or injury.
4. Pura-Fit must only be used as part of a hearing conservation program that complies with applicable local safety and health regulations.
5. Overprotection can be dangerous. The wearer must be able to hear warning signals.
6. Wearers with hearing loss should exercise extreme caution.
7. It is the employer's responsibility to ensure that the type of hearing protector and its SLC₈₀ is appropriate for the user in their particular workplace.
8. Failure to follow these warnings could result in serious injury or death.

MOLDEX TECHNICAL ASSISTANCE

Moldex provides all of the technical assistance required to set up a hearing protection program. For more information call +1 (800) 421-0668 or +1 (310) 837-6500 ext. 512/550 or E-mail: tech@moldex.com or visit www.moldex.com.

DISTRIBUTED BY:

MOLDEX
Ideas that wear well.

MOLDEX-METRIC, INC.
10111 Jefferson Blvd.
Culver City, CA 90232
TEL: +1 (800) 421-0668 or
+1 (310) 837-6500
FAX: +1 (310) 837-9563
E-mail: sales@moldex.com
www.moldex.com

AUSTRALIA
P.O. Box 4086
Carlingford North, NSW 2118
TEL: +61 (02) 9838 7588
E-mail: moldexaustralia@moldex.com
www.moldex.com

NEW ZEALAND
3 Spence Road
Henderson, Auckland, NZ
TEL: +64 (9) 837 8247
FAX: +64 (9) 837 8248
E-mail: moldexnz@moldex.com
www.moldex.com

MX-5 EARMUFFS

ATTENUATION DATA FOR AUSTRALIA / NEW ZEALAND

Tested According to AS/NZS 1270 by Michael & Associates.

Note: For full details of methods of selecting a hearing protector, see AS/NZS 1269.3

Hearing protector Class 5 tested to AS/NZS 1270. When selected, used and maintained as specified in AS/NZS 1269.3, this protector may be used in noise up to 110dB(A) assuming an 85dB(A) criterion.

A lower criterion may require a higher protector class.

| Frequency (Hz) | 125 | 250 | 500 | 1000 | 2000 | 4000 | 8000 | |
|------------------------------------|------|------|------|------|------|------|------|---------------------------------------|
| Mean Attenuation (dB) | 19.0 | 22.1 | 31.4 | 37.2 | 36.8 | 35.1 | 36.6 | SLC ₈₀ 32dB, Class 5 |
| Standard Deviation (dB) | 3.0 | 2.8 | 3.3 | 3.5 | 3.0 | 3.4 | 3.9 | |
| Mean Minus Standard Deviation (dB) | 16.0 | 19.3 | 28.1 | 33.7 | 33.8 | 31.7 | 32.7 | |

MX-6 EARMUFFS

ATTENUATION DATA FOR AUSTRALIA / NEW ZEALAND

Tested According to AS/NZS 1270 by Michael & Associates.

Note: For full details of methods of selecting a hearing protector, see AS/NZS 1269.3

Hearing protector Class 5 tested to AS/NZS 1270. When selected, used and maintained as specified in AS/NZS 1269.3, this protector may be used in noise up to 110dB(A) assuming an 85dB(A) criterion.

A lower criterion may require a higher protector class.

| Frequency (Hz) | 125 | 250 | 500 | 1000 | 2000 | 4000 | 8000 | |
|------------------------------------|------|------|------|------|------|------|------|---------------------------------------|
| Mean Attenuation (dB) | 21.5 | 24.4 | 32.7 | 38.3 | 39.2 | 44.0 | 39.4 | SLC ₈₀ 34dB, Class 5 |
| Standard Deviation (dB) | 3.4 | 2.7 | 3.2 | 3.7 | 3.0 | 3.8 | 4.6 | |
| Mean Minus Standard Deviation (dB) | 18.1 | 21.7 | 29.5 | 34.6 | 36.2 | 40.2 | 34.8 | |

LIMITED WARRANTY: IMPORTANT NOTICE TO AUSTRALIAN PURCHASER

This warranty is provided in addition to other rights and remedies you have under Australian law. Our goods come with guarantees which cannot be excluded under the Australian Consumer Law. You are entitled to replacement or refund for a major failure and to compensation for other reasonably foreseeable loss or damage. You are also entitled to have the goods repaired or replaced if the goods fail to be of acceptable quality and the failure does not amount to a major failure. This limited warranty is made in lieu of all other warranties, express or implied. There are no other warranties which extend beyond this limited warranty or those in the Australian Consumer Law in Schedule 2 to the Competition and Consumer Act 2010 as amended from time to time, or other similar legislation of a state or territory of Australia (Australian Consumer Law). The products sold will meet Moldex's physical standards and specifications. Subject to the Australian Consumer Law, remedies for breach of this limited warranty are limited to replacement of the number of Moldex products proved to have been defectively manufactured. Under this limited warranty, Moldex shall not be liable or responsible for any loss, damage or liability, direct, indirect, special, or consequential, arising out of sale, use, or misuse, or the inability to use products by the user, although you may have other rights and remedies under the Australian Consumer Law. Any claim under the warranty must be made within 1 year of the date of purchase of the product. To make a claim under the warranty, take the product (with proof of purchase) to the store where you purchased the product to contact Moldex. Moldex will pay your reasonable direct expenses of making a claim under this limited warranty which is upheld. You may submit details and proof of your expense claim to Moldex for consideration. This warranty is given by:

Moldex-Metric International LLC • ABN 64 964 843 487
10111 W Jefferson Blvd., Culver City, CA 90232, USA
+1 (310) 837-6500 • sales@moldex.com.



Printed on Recycled Paper