

# EcoStation™

## EARPLUG DISPENSER WITH SEALED SNAP-IN REFILLS



### EASIEST DISPENSER TO REFILL

### INCREASED COMPLIANCE AND COST SAVINGS

Convenient, quick access and ease of use for more compliance. Plus, workers take only one pair at a time, so there is less waste. Less waste means more cost savings. Economical alternative to packaged earplugs.

### LOW INITIAL INVESTMENT

Competitive earplug dispensers are expensive, cumbersome and sometimes don't even come with earplugs! The EcoStation Starter Pack is a lower cost turnkey solution and comes prefilled with 500 pairs of earplugs. More cost effective than other earplug dispensers.

### SNAP-IN REFILL

Easy to install refill, snaps in quickly, for fast changeover. The sealed refill helps prevent contamination.

### SAVE GREEN & BE GREENER

The refillable and recyclable EcoStation dispenser is easy on the hearing protection budget and easy on the environment. Plus it's 100% PVC-Free like all Moldex products and packaging.



### EARPLUGS EVERYWHERE AND ANYWHERE THEY'RE NEEDED

With the EcoStation, you can afford to put earplugs in all the places they're needed. Hang one near workstations, outside the restrooms, in the breakroom, small spaces, and high traffic locations. Easy, convenient access to hearing protection will ensure that the earplugs are being used and will save time.

### HYGIENIC FROM DISPENSER TO YOUR HAND

Earplugs drop right into the palm of your hand so you don't have to worry about plugs falling on the floor or trays collecting dust and contaminants. When the EcoStation is empty simply dispose of it in the recycle bin and replace with an easy to install refill.

### FEATURES & BENEFITS:

- More economical and green than packaged earplugs
- Easy-to-install, sealed refills, snaps in quickly
- Gives workers easy access to hearing protection
- 500 pairs in each EcoStation
- Compliance – High visibility to increase awareness for your hearing conservation program
- Convenience – Hang a EcoStation anywhere and everywhere plugs are needed
- Cost Savings – Workers take one pair at a time so there are no wasteful grabbing of multiple pairs
- Independently tested to AZ/NZS 1270:2002
- 100% PVC-Free

### AVAILABLE EARPLUGS 500 PAIR / ECOSTATION



**Sparkplugs® EcoStation**  
6703 Starter Kit  
6704 Refill  
SLC<sub>80</sub> 29dB  
Class 5



**Pura-Fit® EcoStation**  
6705 Starter Kit  
6706 Refill  
SLC<sub>80</sub> 27dB  
Class 5



**Softies® EcoStation**  
6701 Starter Kit  
6702 Refill  
SLC<sub>80</sub> 29dB  
Class 5

## EARPLUG DISPENSER WITH SEALED SNAP-IN REFILLS

PART # / DESCRIPTION	DISPLAY	CASE
6703 SparkPlugs Starter Kit	500 Pairs	4 Dispensers
6704 SparkPlugs Refill	500 Pairs	4 Dispensers
6705 Pura-Fit Starter Kit	500 Pairs	4 Dispensers
6706 Pura-Fit Refill	500 Pairs	4 Dispensers
6701 Softies Starter Kit	500 Pairs	4 Dispensers
6702 Softies Refill	500 Pairs	4 Dispensers
6868 PlugStation/EcoStation Magnetic Bracket Assembly	1 Bracket/ 1 Envelope	1 Envelope



6868

### WARNING TO USER

- Use these laboratory derived attenuation data for comparison purposes only. The amount of protection afforded in field use often is significantly lower depending upon how the protectors are fitted and worn.
- Failure to obtain a proper fit will reduce effectiveness of hearing protectors and could result in hearing loss or injury.
- Over protection can be dangerous. The wearer must be able to hear warning signals.
- Wearers with hearing loss should exercise extreme caution.
- It is the employer's responsibility to ensure that the type of hearing protector and its rating is appropriate for the user in their particular workplace.
- Failure to follow all instructions and warnings could result in increased risk of hearing loss, serious injury or death.
- Moldex earplugs must only be used as part of a hearing conservation program that complies with applicable local safety and health regulations.

### MOLDEX TECHNICAL ASSISTANCE

Moldex provides all of the technical assistance required to set up a hearing protection program. For more information call +1 (800) 421-0668 or +1 (310) 837-6500 ext. 512/550 or E-mail: tech@moldex.com or visit www.moldex.com.

Keep earplugs away from infants and small children as they may get caught in the windpipe and create a choking hazard.



### ATTENUATION DATA FOR AUSTRALIA / NEW ZEALAND – UNCORDED 6604 SPARKPLUGS AND

Tested According to AS/NZS 1270 by Challis & Associates.  
Note: For full details of methods of selecting a hearing protector, see AS/NZS 1269.3  
Hearing protector Class 5 tested to AS/NZS 1270. When selected, used and maintained as specified in AS/NZS 1269.3, this protector may be used in noise up to 110dB(A) assuming an 85dB(A) criterion. A lower criterion may require a higher protector class.

Frequency (Hz)	125	250	500	1000	2000	4000	8000	
Mean Attenuation (dB)	30.4	32.5	33.1	33.6	36.8	44.9	48.0	<b>SLC<sub>90</sub> 29dB, Class 5</b>
Standard Deviation (dB)	8.7	8.2	9.2	7.8	5.5	7.0	4.9	
Mean Minus Standard Deviation (dB)	21.7	24.3	23.9	25.8	31.3	37.9	43.1	

### ATTENUATION DATA FOR AUSTRALIA / NEW ZEALAND – UNCORDED 6800 PURA-FIT

Tested According to AS/NZS 1270 by Challis & Associates.  
Note: For full details of methods of selecting a hearing protector, see AS/NZS 1269.3  
Hearing protector Class 5 tested to AS/NZS 1270. When selected, used and maintained as specified in AS/NZS 1269.3, this protector may be used in noise up to 110dB(A) assuming an 85 dB(A) criterion. A lower criterion may require a higher protector class.

Frequency (Hz)	125	250	500	1000	2000	4000	8000	
Mean Attenuation (dB)	25.8	25.1	26.2	27.4	35.3	44.6	43.9	<b>SLC<sub>90</sub> 27dB, Class 5</b>
Standard Deviation (dB)	5.7	5.4	6.0	4.3	3.4	5.4	9.1	
Mean Minus Standard Deviation (dB)	20.1	19.7	20.2	23.1	31.9	39.2	34.8	

### ATTENUATION DATA FOR AUSTRALIA / NEW ZEALAND – UNCORDED 6600 SOFTIES

Tested According to AS/NZS 1270 by Challis & Associates.  
Note: For full details of methods of selecting a hearing protector, see AS/NZS 1269.3  
Hearing protector Class 5 tested to AS/NZS 1270. When selected, used and maintained as specified in AS/NZS 1269.3, this protector may be used in noise up to 110dB(A) assuming an 85dB(A) criterion. A lower criterion may require a higher protector class.

Frequency (Hz)	125	250	500	1000	2000	4000	8000	
Mean Attenuation (dB)	30.4	32.5	33.1	33.6	36.8	44.9	48.0	<b>SLC<sub>90</sub> 29dB, Class 5</b>
Standard Deviation (dB)	8.7	8.2	9.2	7.8	5.5	7.0	4.9	
Mean Minus Standard Deviation (dB)	21.7	24.3	23.9	25.8	31.3	37.9	43.1	

### LIMITED WARRANTY: IMPORTANT NOTICE TO AUSTRALIAN PURCHASER

This warranty is provided in addition to other rights and remedies you have under Australian law. Our goods come with guarantees which cannot be excluded under the Australian Consumer Law. You are entitled to replacement or refund for a major failure and to compensation for other reasonably foreseeable loss or damage. You are also entitled to have the goods repaired or replaced if the goods fail to be of acceptable quality and the failure does not amount to a major failure. This limited warranty is made in lieu of all other warranties, express or implied. There are no other warranties which extend beyond this limited warranty or those in the Australian Consumer Law in Schedule 2 to the Competition and Consumer Act 2010 as amended from time to time, or other similar legislation of a state or territory of Australia (Australian Consumer Law). The products sold will meet Moldex's physical standards and specifications. Subject to the Australian Consumer Law, remedies for breach of this limited warranty are limited to replacement of the number of Moldex products proved to have been defectively manufactured. Under this limited warranty, Moldex shall not be liable or responsible for any loss, damage or liability, direct, indirect, special, or consequential, arising out of sale, use, or misuse, or the inability to use products by the user, although you may have other rights and remedies under the Australian Consumer Law. Any claim under the warranty must be made within 1 year of the date of purchase of the product. To make a claim under the warranty, take the product (with proof of purchase) to the store where you purchased the product to contact Moldex. Moldex will pay your reasonable direct expenses of making a claim under this limited warranty which is upheld. You may submit details and proof of your expense claim to Moldex for consideration. This warranty is given by:

Moldex-Metric International LLC • ABN 64 964 843 487  
10111 Jefferson Blvd., Culver City, CA 90232, USA  
+1 (310) 837-6500 • sales@moldex.com.

**MOLDEX**  
Ideas that wear well.™

**MOLDEX-METRIC, INC.**  
10111 Jefferson Blvd.  
Culver City, CA 90232  
TEL: +1 (800) 421-0668 or  
+1 (310) 837-6500  
FAX: +1 (310) 837-9563  
E-mail: sales@moldex.com  
www.moldex.com

**AUSTRALIA**  
P.O. Box 4086  
Carlingford North, NSW 2118  
TEL: +61 (02) 9838 7588  
E-mail: moldexaustralia@moldex.com  
www.moldex.com

**NEW ZEALAND**  
3 Spence Road  
Henderson, Auckland, NZ  
TEL: +027 243 1244  
FAX: +64 (9) 837 8248  
E-mail: moldexnz@moldex.com  
www.moldex.com

